

| DRP                                                                                                                                                                                                                                                                                                                                                                                   |  |  |  | DRP                                                                                                                                                        |  |  |  | Page                                                                                                                                                       |  |  |  |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|--|------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|--|------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|--|
| Performance sheet                                                                                                                                                                                                                                                                                                                                                                     |  |  |  | RX183/005-B                                                                                                                                                |  |  |  | 1/2                                                                                                                                                        |  |  |  |
| CUSTOMER: JSC MZOR                                                                                                                                                                                                                                                                                                                                                                    |  |  |  | CUSTOMER ORDER REF: 80/521-1-2 MZOR                                                                                                                        |  |  |  | EXTERNAL DIMENSIONS & INTERFACES: SN: 902781                                                                                                               |  |  |  |
| DISTRIBUTOR:                                                                                                                                                                                                                                                                                                                                                                          |  |  |  | REDEX ORDER REF: 213474                                                                                                                                    |  |  |  |                                                                                                                                                            |  |  |  |
| DESIGNATION: DRP2+R.31.4.H                                                                                                                                                                                                                                                                                                                                                            |  |  |  | SERIAL NUMBER: 902781                                                                                                                                      |  |  |  |                                                                                                                                                            |  |  |  |
| CODE: RX128950-12                                                                                                                                                                                                                                                                                                                                                                     |  |  |  | MOTOR FLANGE CODE: RX129627-01                                                                                                                             |  |  |  |                                                                                                                                                            |  |  |  |
| <p>Mechanical preload data</p> <p>The preload torque of the gearbox in DUALDRIVE configuration depends on the application data and features of the gearbox.</p> <p>The preload torque can be increased but must never exceed the maximum value indicated below.</p> <p>A too important preload torque reduces the efficiency and the life expectancy of the gearbox and the rack.</p> |  |  |  |                                                                                                                                                            |  |  |  |                                                                                                                                                            |  |  |  |
| <p>Optimal preload torque Tp:</p> <p>Maximum preload torque:</p>                                                                                                                                                                                                                                                                                                                      |  |  |  | <p>Following application</p> <p>18,7 Nm</p>                                                                                                                |  |  |  |                                                                                                                                                            |  |  |  |
| <p>For the installation, please refer to User Manual DRP (182/009)</p>                                                                                                                                                                                                                                                                                                                |  |  |  |                                                                                                                                                            |  |  |  |                                                                                                                                                            |  |  |  |
| <p>SPECIFIC REMARKS:</p>                                                                                                                                                                                                                                                                                                                                                              |  |  |  |                                                                                                                                                            |  |  |  |                                                                                                                                                            |  |  |  |
| <p>Product images are for illustrative purposes only.</p>                                                                                                                                                                                                                                                                                                                             |  |  |  |                                                                                                                                                            |  |  |  |                                                                                                                                                            |  |  |  |
| <p><b>REDEX</b></p> <p>ZI-BP79<br/>F45210 FERRIERES<br/>www.redex.fr</p> <p>Tel: +33 2 38 94 42 00<br/>Fax: +33 2 38 94 42 99<br/>Email: info@redex.fr</p>                                                                                                                                                                                                                            |  |  |  | <p><b>REDEX</b></p> <p>ZI-BP79<br/>F45210 FERRIERES<br/>www.redex.fr</p> <p>Tel: +33 2 38 94 42 00<br/>Fax: +33 2 38 94 42 99<br/>Email: info@redex.fr</p> |  |  |  | <p><b>REDEX</b></p> <p>ZI-BP79<br/>F45210 FERRIERES<br/>www.redex.fr</p> <p>Tel: +33 2 38 94 42 00<br/>Fax: +33 2 38 94 42 99<br/>Email: info@redex.fr</p> |  |  |  |